

### **Key Features**

- 4 x SFP+ channels at 10 Gbps each
- PCIe Gen3 x8 Half-length card
- · 4GB onboard video cache
- Flexible machine I/O:
  - 4 TTL configurable I/Os
  - 4 LVCMOS configurable I/Os
  - · 2 LVDS inputs
  - · 2 LVDS outputs
  - · 4 opto-isolated outputs
  - 4 opto-isolated inputs
  - · 2 quadrature rotary encoders
  - · Integrated strobe controller
  - 4 timers
- · Optical interface
- Transfer Rate of up to 55 Gbps through PCIe
- Transfer Rate of up to 40 Gbps through optical interfaces
- CWDM support
- · Authentication device for design security
- Temperature control
- Fan control
- GUI interface
- · Supporting Windows and Linux OS
- API for developing custom applications
- Plug-ins modules for Matlab, HALCON and Labview
- Gen<i>Cam compliant
- GenTL support
- 4 indication LEDs
- O°C to 55°C operating environment temperature

# Komodo II<sup>™</sup> Fiber Frame Grabber


### **Innovative Approach**

Komodo II Fiber is high-performance yet low-cost FPGA card supporting four SFP+ 10GigE transceivers optical interface. The card is based on powerful FPGA, a DDR4 memory system with 4GB onboard video cache and 55 Gbps throughput. A high speed 8 lane Gen 3.0 PCI express interface allows fast data transfers between optical links and computer memory while a versatile GPIO with multi-standard support enables connection to external devices. The SFP+ interfaces are connected directly to FPGA device transceiver channels to minimize latency.

### **Intelligent Design**

All of these features combine make the Komodo II Fiber ideal for a wide range of applications, including network processing and security, compute and storage, instrumentation, broadcast, defense and aerospace.

## Datasheet | Komodo II™ Fiber Frame Grabber




Product Name	Komodo II Fiber Frame Grabber
Form Factor	PCI Express card
Format	Standard profile, half length, 8-lane PCI Express card
Cooling method	Air cooling, fan-cooled heatsink (Optional passive bracket)
Mounting	For insertion in a standard height, 8-lane or higher, PCI Express card slot
Connectors	4x SFP+ connectors 1x Internal I/O connector: 26-pin 2-row 0.1" pitch pin header with shrouding for I/O lines 1x External I/O connector on bracket: DB15 - 15-pin 3-row D-Sub High density, panel mount, through hole, right angle
Dimensions	L 167.65 mm x H 111.15 mm L 6.6 in x H 4.38 in
Weight	225gr
Hot bus Standard	PCI Express 3.0
Link width	8 lanes, 1, 2 or 4 lanes with reduced performance
Link speed	<ul> <li>8.0 GT/s (PCIe 3.0)</li> <li>5.0 GT/s (PCIe 2.0) with reduced performance</li> </ul>
Maximum payload size	512 bytes
DMA	<ul> <li>32- and 64-bit</li> <li>Scatter gather support</li> <li>Physical address support (GPU transfers)</li> </ul>
Peak delivery bandwidth	7,880 MB/s
Effective (sustained), delivery bandwidth	6,710 MB/s (Host PC motherboard dependent)
Power consumption	Typ. 16.8 W (3.8 W @ +3.3V, 13 W @ +12V), excluding camera and I/O power output
Camera / video inputs	
Interface standard(s)	10GiGE Vision, CLHS X protocol
Status LEDs	1 Host connection status per connector 4 System status LEDs
Number of cameras	Up to 4
Number of links, per single camera	Up to 4
Synchronization between cameras	Yes
Line-scan cameras supported	Yes
Maximum aggregated camera data transfer rate	40 Gbit/s
Camera types	Area-scan cameras: • Gray-scale and color (RGB and Bayer CFA) • Single-tap (1X-1Y) progressive-scan Line-scan cameras: • Gray-scale and color RGB

Camera pixel formats supported	Raw, Monochrome, Bayer, RGB, YUV, YCbCr and RGBA (PFNC names): • Raw
	<ul> <li>Raw</li> <li>Mono8, Mono10, Mono12, Mono14, Mono16</li> </ul>
	BayerXX8, BayerXX10, BayerXX12, BayerXX14, BayerXX16
	where $XX = GR$ , RG, GB, or BG
	• RGB8, RGB10, RGB12, RGB14, RGB16
	• YUV411_8, YUV411_10, YUV411_12, YUV411_14, YUV411_16
	• YUV422_8, YUV422_10, YUV422_12, YUV422_14, YUV422_16
	• YUV444_8, YUV444_10, YUV444_12, YUV444_14, YUV444_16
	• YCbCr601_411_8, YCbCr601_411_10, YCbCr601_411_12,
	YCbCr601_411_14, YCbCr601_411_16 • YCbCr601_422_8, YCbCr601_422_10, YCbCr601_422_12,
	YCbCr601_422_14, YCbCr601_422_16
	• YCbCr601_444_8, YCbCr601_444_10, YCbCr601_444_12,
	YCbCr601_444_14, YCbCr601_444_16
Area-scan camera control	
Trigger	Precise control of asynchronous reset cameras, with exposure
	control. Support of camera exposure/readout overlap.
	Support of triggering from encoder or timer.
	Support of external hardware trigger, with optional delay, filtering
	and trigger decimation.
Strobe	Accurate control of the strobe position for strobe light sources.
	Support of early and late strobe pulses.
Line-scan camera control	Drasics control of start of econ and and of econ trianers
Scan/page trigger	Precise control of start-of-scan and end-of-scan triggers. Support of external hardware trigger, with optional delay and
	filtering.
	Support of triggering from encoder.
	Support of infinite acquisition, without missing lines.
Line trigger	Support for quadrature motion encoders, with programmable filters,
	selection of acquisition direction and backward motion
	compensation.
Line strobe	Accurate control of the strobe position for strobe light sources.
On-board processing On-board memory	
	Up to 4GByte SODIMM
Bayer De-Mosaic	Full 16bit resolution <ul> <li>Bilinear 3x3</li> </ul>
	Bilinear 3x2 for linescan with gradient correction
Color Transformation	Full 16bit resolution 18bit coefficients table
	Color space conversion
	Gain and Offset
Decimation	Line skip
Additional features	Unpacking of 10-/12-/14-bit to 16-bit with justification to LSB
Frame Timestamp	64bit with 8ns precision
Data stream statistics	Measurement of:
	• Frame/Line rate
	CRC Errors
	Dropped frames     Pessived packets
	<ul> <li>Received packets</li> <li>Test packets</li> </ul>
Event signaling and counting	The application software can be notified of the occurrence of
	various events:
	Newly acquired buffers
	Camera and Illumination control events
	• I/O events
	<ul> <li>Timer events</li> <li>Encoder events</li> </ul>
General Purpose Inputs and Outputs	
Number of lines	20 I/O lines:
	2 differential inputs
	2 differential outputs
	4 singled-ended TTL inputs/outputs 4 singled-ended LVCTTL inputs/outputs

	4 opto-isolated inputs
Lleave	4 opto-isolated outputs
Usage	Any System I/O input lines can be connected to any I/O line Any I/O line can be used to decode A/B and Z signals of a motion
	encoder
	Any I/O line can generate any trigger event Any I/O line can trigger a timer
Electrical specifications	Differential lines - LVDS compatible
	TTL lines - 5V TTL compliant
	LVTTL lines - 3.3V LVTTL compliant
	Isolated lines - opto isolated lines with voltage range up to 30V
Filter control	Glitch removal filter available on all System I/O input lines Configurable filter time constants
	for DIN and TTLIO lines: 50 ns, 100 ns, 200 ns, 500 ns,1 µs
	for IIN lines: 500 ns, 1 μs, 2 μs, 5 μs, 10 μs
Polarity control	Yes
Encoders	4 quadrature encoders with A/B and Z inputs
	32bit position counter Forward and backward counting
	Position trigger support
	Noise filtering
Timers	4 general purpose timers
	Configurable delay and duration 32bit accumulator
Event reporting	64bit system timestamp event reporting
Event reporting	Each I/O line can generate event on configurable edge
	Each Timer can generate event
	Each encoder can generate event
Frame grabber synchronization Synchronization	Brasica area and lineacon comerce synchronization across
Synchronization	Precise area and linescan cameras synchronization across different frame grabbers
Software	
Host PC Operating System	Microsoft Windows 7/10 32- and 64-bit versions, Linux open
	source driver compatible with a wide range of distributions, tested
	and precompiled for Ubuntu 14.04 , RedHat 6.5 , CentOS 7 32- and 64-bit versions
Buffer management	Circular buffer support
-	Accumulation of several frames/lines to single buffer to reduce
	CPU load
Gen <i>Cam</i>	DMA Buffer filling directly to system memory Support of Gen <i>Cam up to 2.4</i>
	Full camera and frame grabber parameters configuration
GUI	Supported for Windows and Linux OS
	Multicamera display and configuration
	Flexible buffer queuing Image/video recording and playback
Debugging capabilities	Event logging
	Statistics counters
Environmental conditions	
Operating ambient air temperature	0°C to +50°C / +32°F to +122 °F
Operating ambient air humidity	10% to 90% RH non-condensing
Storage ambient air temperature	-20°C to +70°C / -4°F to +158°F
Storage ambient air humidity	10% to 90% RH non-condensing
Certifications	
Electromagnetic - EMC standards	The European Council EMC Directive 2004/108/EC
EMC - Emission	The Unites States FCC rule 47 CFR 15 EN 55022:2010 Class B
	FCC 47 Part 15 Class B
EMC - Immunity	EN 55024:2010 Class B
	EN 61000-4-3
	EN 61000-4-4 EN 61000-4-6
Flammability	PCB compliant with UL 94 V-0

REACH	Compliant with the European Union Regulation No 1907/2006
WEEE	Must be disposed of separately from normal household waste and must be recycled according to local regulations
Ordering Information	KY-FGFII
Optional accessories	
	<ul> <li>DDR4 SODIMM 2GB, 4GB, 8GB or 16GB</li> <li>SFP+ optical modules</li> <li>Fiber cables</li> </ul>

### Komodo II Fiber Frame Grabber HW Block Diagram



### Compatibility

Supported vision standard

GENCIALAYER DGIGE GENTL COAXPress

Supported operating systems



Supported vision libraries

Worldwide

KAYA Instruments 20 HaMesila St. Nesher 3688520 POB 25004, Haifa 3125001 Israel

info@kayainstruments.com

Tel: +972 72 272 3500 Fax: +972 72 272 3511



Compatible with most popular machine vision libraries

KAYA Instrument strives to create and maintain compatibility and interfaces for the most common and advanced vision image processing libraries and applications. Major support is available for **MVTec Halcon, National Instruments LabVIEW** and **MathWorks MATLAB**. Please check our KAYA website for an upto-date list of other supported libraries and software package.

Get in touch with our teams at **info@kayainstruments.com**. We will be glad to assist and consult you regarding our products.

The information provided here is subject to change without notice

Contact





#### http://www.kayainstruments.com/products/frame-grabbers/

© 2017 KAYA Instruments, Inc. All rights reserved. KAYA Instruments, the KAYA Instruments Komodo logo, JetCam logo, Predator and combinations thereof are trademarks of KAYA Instruments, Inc. in the United States and/or other jurisdictions. Microsoft Windows is a registered trademark of Microsoft Corporation. Other names are for informational purposes only and may be trademarks of their respective owners. KAYA Instruments is not liable for harm or damage incurred by information contained in this document. KY-DOC-FGF